

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263745

Luminaire Tested: P3AS02R129730DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129730DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 224.0 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263745

CATALOG NUMBER: P3AS02R129730DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1263745

CATALOG NUMBER: P3AS02R129730DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	90	89
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	86	85
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	82	81
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	80	79	78
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	76	75
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	73	72
8	89	81	77	74	88	81	77	73	80	76	73	79	76	73	78	75	73	72	71	70
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	68	67
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191344
5°	169865
10°	117967
15°	69762
20°	39740
25°	22719
30°	12559
35°	6692
40°	3693
45°	2016
50°	1262
55°	994
60°	833
65°	778
70°	705
75°	763
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2016 cd/sqm

TEST NUMBER: P1263745

CATALOG NUMBER: P3AS02R129730DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	29.3
10°-20°	86.6	38.7
20°-30°	44.6	19.9
30°-40°	16.7	7.5
40°-50°	5.5	2.4
50°-60°	2.4	1.1
60°-70°	1.5	0.7
70°-80°	0.9	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.8	87.9
0°-40°	213.5	95.3
0°-60°	221.4	98.8
0°-90°	224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	224.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	873	
5°	772	66
15°	307	87
25°	94	45
35°	25	17
45°	6	5
55°	3	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263745

CATALOG NUMBER: P3AS02R129730DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	872.6
1°	870.9
2°	859.5
3°	837.7
4°	809.0
5°	771.7
6°	729.4
7°	683.0
8°	631.4
9°	580.5
10°	529.8
12.5°	407.6
15°	307.3
17.5°	230.0
20°	170.3
22.5°	127.1
25°	93.9
27.5°	68.4
30°	49.6
32.5°	35.2
35°	25.0
37.5°	17.9
40°	12.9
42.5°	9.3
45°	6.5
47.5°	4.7
50°	3.7
52.5°	3.0
55°	2.6
57.5°	2.2
60°	1.9
62.5°	1.7
65°	1.5
67.5°	1.3
70°	1.1
72.5°	1.1
75°	0.9
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)