

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264385

Luminaire Tested: P3AS05R509730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 248.0 lumens
Efficiency: N/A
Efficacy: 34.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264385
CATALOG NUMBER: P3AS05R509730DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1264385
 CATALOG NUMBER: P3AS05R509730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	68	68	68	68
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78963
5°	77372
10°	72477
15°	64881
20°	54605
25°	41664
30°	27067
35°	16062
40°	9275
45°	4652
50°	1740
55°	1338
60°	1272
65°	1141
70°	1154
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4652 cd/sqm



TEST NUMBER: P1264385
 CATALOG NUMBER: P3AS05R509730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.7	13.2
10°-20°	79.0	31.9
20°-30°	77.5	31.3
30°-40°	39.1	15.8
40°-50°	12.3	5.0
50°-60°	3.2	1.3
60°-70°	2.3	0.9
70°-80°	1.4	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.3	76.3
0°-40°	228.3	92.1
0°-60°	243.9	98.3
0°-90°	248.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	248.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	360	
5°	352	33
15°	286	79
25°	172	78
35°	60	39
45°	15	12
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1264385
CATALOG NUMBER: P3AS05R509730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	360.1
2.5°	357.9
5°	351.5
7.5°	340.0
10°	325.5
12.5°	306.7
15°	285.8
17.5°	261.5
20°	234.0
22.5°	204.2
25°	172.2
27.5°	138.3
30°	106.9
32.5°	80.5
35°	60.0
37.5°	44.3
40°	32.4
42.5°	22.9
45°	15.0
47.5°	8.6
50°	5.1
52.5°	3.7
55°	3.5
57.5°	3.1
60°	2.9
62.5°	2.6
65°	2.2
67.5°	2.0
70°	1.8
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)