

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264414

Luminaire Tested: P3AS05R559730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 240.0 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264414
CATALOG NUMBER: P3AS05R559730DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1264414
 CATALOG NUMBER: P3AS05R559730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87				87
3	102	96	91	87	100	95	90	86	92	88	85	89	86	84	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75				75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65894
5°	65243
10°	62991
15°	58230
20°	50241
25°	39680
30°	28156
35°	18150
40°	10906
45°	6140
50°	3309
55°	1185
60°	1053
65°	1038
70°	962
75°	932
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6140 cd/sqm



TEST NUMBER: P1264414
 CATALOG NUMBER: P3AS05R559730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.9	11.6
10°-20°	70.9	29.6
20°-30°	74.3	31.0
30°-40°	43.4	18.1
40°-50°	16.2	6.8
50°-60°	3.8	1.6
60°-70°	2.0	0.8
70°-80°	1.2	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.1	72.1
0°-40°	216.5	90.2
0°-60°	236.5	98.6
0°-90°	240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	300	
5°	296	28
15°	256	71
25°	164	74
35°	68	43
45°	20	16
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1264414
CATALOG NUMBER: P3AS05R559730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	300.5
2.5°	299.7
5°	296.4
7.5°	291.1
10°	282.9
12.5°	271.5
15°	256.5
17.5°	237.6
20°	215.3
22.5°	190.5
25°	164.0
27.5°	136.9
30°	111.2
32.5°	87.8
35°	67.8
37.5°	51.5
40°	38.1
42.5°	27.3
45°	19.8
47.5°	14.3
50°	9.7
52.5°	5.5
55°	3.1
57.5°	2.6
60°	2.4
62.5°	2.2
65°	2.0
67.5°	1.8
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)