

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263802

Luminaire Tested: P3AS02R209730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 111.0 lumens
Efficiency: N/A
Efficacy: 30.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263802

CATALOG NUMBER: P3AS02R209730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263802

CATALOG NUMBER: P3AS02R209730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	86	78	73	70	85	77	73	70	77	73	70		76	72	70		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85410
5°	77636
10°	57380
15°	35483
20°	20278
25°	11565
30°	6482
35°	3534
40°	1947
45°	1054
50°	614
55°	459
60°	439
65°	415
70°	321
75°	339
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1054 cd/sqm

TEST NUMBER: P1263802

CATALOG NUMBER: P3AS02R209730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.5	27.5
10°-20°	43.6	39.3
20°-30°	22.8	20.5
30°-40°	8.8	7.9
40°-50°	2.9	2.6
50°-60°	1.1	1.0
60°-70°	0.8	0.7
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	96.9	87.3
0°-40°	105.7	95.2
0°-60°	109.7	98.8
0°-90°	111.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	111.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	390	
5°	353	31
15°	156	44
25°	48	23
35°	13	9
45°	3	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1263802

CATALOG NUMBER: P3AS02R209730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	389.5
1°	388.7
2°	384.1
3°	377.0
4°	366.1
5°	352.7
6°	336.8
7°	319.2
8°	298.9
9°	279.0
10°	257.7
12.5°	204.8
15°	156.3
17.5°	117.0
20°	86.9
22.5°	64.3
25°	47.8
27.5°	35.3
30°	25.6
32.5°	18.6
35°	13.2
37.5°	9.5
40°	6.8
42.5°	4.8
45°	3.4
47.5°	2.5
50°	1.8
52.5°	1.4
55°	1.2
57.5°	1.1
60°	1.0
62.5°	0.9
65°	0.8
67.5°	0.6
70°	0.5
72.5°	0.5
75°	0.4
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)