

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263807

Luminaire Tested: P3AS02R209730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 84.0 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263807

CATALOG NUMBER: P3AS02R209730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263807

CATALOG NUMBER: P3AS02R209730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20788
5°	20229
10°	18592
15°	16368
20°	14048
25°	11807
30°	9546
35°	7254
40°	5153
45°	3411
50°	2115
55°	1376
60°	1272
65°	1141
70°	1090
75°	1017
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3411 cd/sqm

TEST NUMBER: P1263807

CATALOG NUMBER: P3AS02R209730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.5	10.1
10°-20°	20.1	23.9
20°-30°	22.3	26.5
30°-40°	17.0	20.2
40°-50°	8.7	10.4
50°-60°	3.6	4.3
60°-70°	2.2	2.6
70°-80°	1.3	1.5
80°-90°	0.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	50.9	60.6
0°-40°	67.9	80.8
0°-60°	80.1	95.4
0°-90°	84.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	84.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	95	
5°	92	8
15°	72	20
25°	49	22
35°	27	17
45°	11	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263807

CATALOG NUMBER: P3AS02R209730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	94.8
1°	94.9
2°	94.4
3°	93.9
4°	93.0
5°	91.9
6°	90.5
7°	89.0
8°	87.4
9°	85.5
10°	83.5
12.5°	78.0
15°	72.1
17.5°	66.2
20°	60.2
22.5°	54.2
25°	48.8
27.5°	43.3
30°	37.7
32.5°	32.3
35°	27.1
37.5°	22.5
40°	18.0
42.5°	14.2
45°	11.0
47.5°	8.3
50°	6.2
52.5°	4.6
55°	3.6
57.5°	3.3
60°	2.9
62.5°	2.6
65°	2.2
67.5°	1.9
70°	1.7
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)