

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264468

Luminaire Tested: P3AS05R659730DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659730DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 536.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264468

CATALOG NUMBER: P3AS05R659730DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1264468

CATALOG NUMBER: P3AS05R659730DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	88	93	89	86		90	87	85		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143629
5°	133370
10°	128967
15°	124291
20°	114903
25°	104692
30°	80873
35°	46873
40°	18606
45°	7939
50°	1876
55°	268
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7939 cd/sqm

TEST NUMBER: P1264468

CATALOG NUMBER: P3AS05R659730DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	10.7
10°-20°	152.5	28.5
20°-30°	193.1	36.0
30°-40°	109.9	20.5
40°-50°	21.9	4.1
50°-60°	1.1	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	402.8	75.1
0°-40°	512.7	95.7
0°-60°	535.7	99.9
0°-90°	536.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	536.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	655	
5°	606	57
15°	548	153
25°	433	193
35°	175	110
45°	26	22
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1264468

CATALOG NUMBER: P3AS05R659730DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	655.0
1°	650.1
2°	639.6
3°	627.2
4°	615.1
5°	605.9
6°	599.0
7°	593.5
8°	588.7
9°	583.8
10°	579.2
11°	574.1
12°	568.8
13°	562.5
14°	555.6
15°	547.5
16°	537.8
17°	527.2
18°	515.7
19°	503.6
20°	492.4
21°	480.9
22°	470.6
23°	459.8
24°	447.2
25°	432.7
26°	415.3
27°	394.4
28°	370.8
29°	345.7
30°	319.4
31°	290.6
32°	261.9
32.5°	247.2
33°	232.9
34°	203.8
35°	175.1
36°	148.7
37°	122.5
37.5°	109.1
38°	98.3
39°	79.5
40°	65.0
42.5°	40.1
45°	25.6

TEST NUMBER: P1264468

CATALOG NUMBER: P3AS05R659730DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	15.0
50°	5.5
52.5°	1.1
55°	0.7
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)