

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263823

Luminaire Tested: P3AS02R259730DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259730DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 295.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263823
CATALOG NUMBER: P3AS02R259730DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1263823
 CATALOG NUMBER: P3AS02R259730DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	83	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81
9	93	87	83	81	92	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	323088
5°	299295
10°	231570
15°	110602
20°	36473
25°	15364
30°	5950
35°	2570
40°	859
45°	403
50°	136
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 403 cd/sqm



TEST NUMBER: P1263823
 CATALOG NUMBER: P3AS02R259730DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.5	40.5
10°-20°	135.9	46.1
20°-30°	31.6	10.7
30°-40°	6.6	2.2
40°-50°	1.1	0.4
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	287.0	97.3
0°-40°	293.7	99.6
0°-60°	294.9	100.0
0°-90°	295.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	295.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1473	
5°	1360	120
15°	487	136
25°	64	32
35°	10	7
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263823
CATALOG NUMBER: P3AS02R259730DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1473.4
1°	1470.4
2°	1455.1
3°	1433.6
4°	1400.7
5°	1359.7
6°	1306.9
7°	1251.7
8°	1189.8
9°	1120.0
10°	1040.0
11°	947.2
12°	840.8
13°	724.2
14°	602.3
15°	487.2
16°	385.4
17°	300.2
18°	236.2
19°	188.9
20°	156.3
21°	130.6
22°	109.6
23°	91.6
24°	76.6
25°	63.5
27.5°	37.6
30°	23.5
32.5°	15.1
35°	9.6
37.5°	5.8
40°	3.0
42.5°	1.9
45°	1.3
47.5°	0.7
50°	0.4
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0



TEST NUMBER: P1263823
CATALOG NUMBER: P3AS02R259730DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)