

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264472

Luminaire Tested: P3AS05R659730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 221.0 lumens
Efficiency: N/A
Efficacy: 30.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264472

CATALOG NUMBER: P3AS05R659730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264472

CATALOG NUMBER: P3AS05R659730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52123
5°	51486
10°	49543
15°	46402
20°	41747
25°	35446
30°	27726
35°	19756
40°	12939
45°	8001
50°	4060
55°	1415
60°	1272
65°	1245
70°	1154
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8001 cd/sqm

TEST NUMBER: P1264472

CATALOG NUMBER: P3AS05R659730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.0	9.9
10°-20°	56.9	25.7
20°-30°	66.5	30.1
30°-40°	46.5	21.0
40°-50°	20.4	9.3
50°-60°	4.6	2.1
60°-70°	2.3	1.0
70°-80°	1.4	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	145.3	65.8
0°-40°	191.8	86.8
0°-60°	216.8	98.1
0°-90°	221.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	221.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	238	
5°	234	22
15°	204	57
25°	146	66
35°	74	46
45°	26	20
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264472

CATALOG NUMBER: P3AS05R659730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	237.7
2.5°	236.8
5°	233.9
7.5°	229.1
10°	222.5
12.5°	214.3
15°	204.4
17.5°	192.3
20°	178.9
22.5°	163.7
25°	146.5
27.5°	128.4
30°	109.5
32.5°	91.2
35°	73.8
37.5°	58.6
40°	45.2
42.5°	34.1
45°	25.8
47.5°	18.9
50°	11.9
52.5°	6.2
55°	3.7
57.5°	3.3
60°	2.9
62.5°	2.6
65°	2.4
67.5°	2.0
70°	1.8
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)