

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264480

Luminaire Tested: P3AS05R659730DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264480  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R659730DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 353.9 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264480  
CATALOG NUMBER: P3AS05R659730DE010 E3DLD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1264480  
 CATALOG NUMBER: P3AS05R659730DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82			82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			74
4	92	83	77	72	90	82	76	71	80	75	71	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	62999
5°	62139
10°	60075
15°	56641
20°	52248
25°	47422
30°	42006
35°	35737
40°	28453
45°	20064
50°	11667
55°	6346
60°	5921
65°	5344
70°	4873
75°	4575
80°	3915
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20064 cd/sqm



TEST NUMBER: P1264480  
 CATALOG NUMBER: P3AS05R659730DE010 E3DLD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.6	7.5
10°-20°	69.8	19.7
20°-30°	89.7	25.3
30°-40°	83.0	23.4
40°-50°	50.1	14.2
50°-60°	17.1	4.8
60°-70°	10.3	2.9
70°-80°	5.8	1.6
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.1	52.6
0°-40°	269.1	76.0
0°-60°	336.2	95.0
0°-90°	353.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	353.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	287	
5°	282	27
15°	250	70
25°	196	90
35°	134	83
45°	65	50
55°	17	17
65°	10	10
75°	5	6
85°	1	2
90°	0	

TEST NUMBER: P1264480  
CATALOG NUMBER: P3AS05R659730DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	287.3
2.5°	285.9
5°	282.3
7.5°	276.9
10°	269.8
12.5°	260.8
15°	249.5
17.5°	237.4
20°	223.9
22.5°	210.0
25°	196.0
27.5°	181.2
30°	165.9
32.5°	150.6
35°	133.5
37.5°	116.9
40°	99.4
42.5°	81.8
45°	64.7
47.5°	49.0
50°	34.2
52.5°	21.6
55°	16.6
57.5°	14.8
60°	13.5
62.5°	11.7
65°	10.3
67.5°	9.0
70°	7.6
72.5°	6.7
75°	5.4
77.5°	4.5
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0

(END OF REPORT)