

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264488

Luminaire Tested: P3AS05R659730DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659730DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 449.9 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264488
CATALOG NUMBER: P3AS05R659730DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1264488
 CATALOG NUMBER: P3AS05R659730DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106132
5°	104842
10°	100867
15°	94484
20°	84987
25°	72174
30°	56439
35°	40234
40°	26306
45°	16281
50°	8256
55°	2906
60°	2544
65°	2542
70°	2308
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16281 cd/sqm



TEST NUMBER: P1264488
 CATALOG NUMBER: P3AS05R659730DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	9.9
10°-20°	115.8	25.7
20°-30°	135.4	30.1
30°-40°	94.6	21.0
40°-50°	41.6	9.3
50°-60°	9.3	2.1
60°-70°	4.7	1.0
70°-80°	2.8	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.0	65.8
0°-40°	390.6	86.8
0°-60°	441.5	98.1
0°-90°	449.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	449.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	484	
5°	476	45
15°	416	116
25°	298	135
35°	150	95
45°	52	42
55°	8	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1264488
CATALOG NUMBER: P3AS05R659730DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	484.0
2.5°	482.2
5°	476.3
7.5°	466.5
10°	453.0
12.5°	436.4
15°	416.2
17.5°	391.6
20°	364.2
22.5°	333.3
25°	298.3
27.5°	261.5
30°	222.9
32.5°	185.7
35°	150.3
37.5°	119.3
40°	91.9
42.5°	69.5
45°	52.5
47.5°	38.6
50°	24.2
52.5°	12.6
55°	7.6
57.5°	6.7
60°	5.8
62.5°	5.4
65°	4.9
67.5°	4.0
70°	3.6
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)