

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263844

Luminaire Tested: P3AS02R259730DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259730DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 229.0 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263844

CATALOG NUMBER: P3AS02R259730DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1263844

CATALOG NUMBER: P3AS02R259730DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146896
5°	137046
10°	109795
15°	74529
20°	45084
25°	26372
30°	15015
35°	8272
40°	4380
45°	2295
50°	1330
55°	994
60°	877
65°	934
70°	833
75°	763
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2295 cd/sqm

TEST NUMBER: P1263844

CATALOG NUMBER: P3AS02R259730DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.3	24.1
10°-20°	90.2	39.4
20°-30°	51.6	22.5
30°-40°	20.4	8.9
40°-50°	6.2	2.7
50°-60°	2.5	1.1
60°-70°	1.7	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	197.1	86.1
0°-40°	217.4	94.9
0°-60°	226.1	98.7
0°-90°	229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	229.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	670	
5°	623	55
15°	328	90
25°	109	52
35°	31	20
45°	7	6
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263844

CATALOG NUMBER: P3AS02R259730DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	669.9
1°	668.6
2°	663.1
3°	653.5
4°	640.1
5°	622.6
6°	602.1
7°	578.9
8°	551.9
9°	524.4
10°	493.1
11°	462.2
12°	428.3
13°	394.8
14°	360.4
15°	328.3
17.5°	254.5
20°	193.2
22.5°	145.1
25°	109.0
27.5°	80.8
30°	59.3
32.5°	42.9
35°	30.9
37.5°	21.9
40°	15.3
42.5°	10.5
45°	7.4
47.5°	5.3
50°	3.9
52.5°	3.1
55°	2.6
57.5°	2.4
60°	2.0
62.5°	1.8
65°	1.8
67.5°	1.5
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1263844

CATALOG NUMBER: P3AS02R259730DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)