

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264512

Luminaire Tested: P3AS05R709730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 323.0 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264512

CATALOG NUMBER: P3AS05R709730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264512

CATALOG NUMBER: P3AS05R709730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75761
5°	74378
10°	70139
15°	63655
20°	55678
25°	46962
30°	38462
35°	29821
40°	21354
45°	13521
50°	6755
55°	4129
60°	3552
65°	3269
70°	2885
75°	2626
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13521 cd/sqm

TEST NUMBER: P1264512

CATALOG NUMBER: P3AS05R709730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.5	9.8
10°-20°	78.0	24.2
20°-30°	88.8	27.5
30°-40°	69.5	21.5
40°-50°	34.2	10.6
50°-60°	10.5	3.2
60°-70°	6.2	1.9
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	198.4	61.4
0°-40°	267.9	82.9
0°-60°	312.5	96.8
0°-90°	323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	323.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	346	
5°	338	32
15°	280	78
25°	194	89
35°	111	69
45°	44	34
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1264512

CATALOG NUMBER: P3AS05R709730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	345.5
2.5°	343.7
5°	337.9
7.5°	328.4
10°	315.0
12.5°	299.2
15°	280.4
17.5°	260.1
20°	238.6
22.5°	216.1
25°	194.1
27.5°	172.5
30°	151.9
32.5°	131.2
35°	111.4
37.5°	92.6
40°	74.6
42.5°	58.0
45°	43.6
47.5°	30.6
50°	19.8
52.5°	13.0
55°	10.8
57.5°	9.4
60°	8.1
62.5°	7.2
65°	6.3
67.5°	5.4
70°	4.5
72.5°	3.6
75°	3.1
77.5°	2.7
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)