

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263859

Luminaire Tested: P3AS02R309730DE010 E3D1WMH

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1263859  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R309730DE010 E3D1WMH  
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 276.0 lumens  
Efficiency: N/A  
Efficacy: 76.7 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263859

CATALOG NUMBER: P3AS02R309730DE010 E3D1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1263859

CATALOG NUMBER: P3AS02R309730DE010 E3D1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 |  | 103 | 102 | 101 |  | 100 |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  |  | 100 | 98  | 97  |  | 97  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 97  | 95  |  | 97  | 95  | 93  |  | 95  |
| 4   | 105 | 99  | 95  | 92  | 103 | 98  | 95  | 92  | 96  | 93  | 91  |  | 94  | 92  | 90  |  | 93  |
| 5   | 101 | 96  | 92  | 89  | 100 | 95  | 91  | 88  | 93  | 90  | 87  |  | 92  | 89  | 87  |  | 90  |
| 6   | 99  | 92  | 88  | 85  | 97  | 92  | 88  | 85  | 90  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 7   | 96  | 89  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  |  | 87  | 84  | 81  |  | 86  |
| 8   | 93  | 87  | 83  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  |  | 84  | 81  | 79  |  | 84  |
| 9   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  |  | 82  | 79  | 77  |  | 82  |
| 10  | 88  | 82  | 78  | 75  | 88  | 81  | 78  | 75  | 81  | 77  | 75  |  | 80  | 77  | 75  |  | 80  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 219588 |
| 5°  | 216728 |
| 10° | 189219 |
| 15° | 120273 |
| 20° | 47651  |
| 25° | 15920  |
| 30° | 7394   |
| 35° | 3346   |
| 40° | 1288   |
| 45° | 620    |
| 50° | 171    |
| 55° | 76     |
| 60° | 44     |
| 65° | 52     |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 620 cd/sqm

TEST NUMBER: P1263859

CATALOG NUMBER: P3AS02R309730DE010 E3D1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 90.0   | 32.6      |
| 10°-20°   | 139.6  | 50.6      |
| 20°-30°   | 36.0   | 13.0      |
| 30°-40°   | 8.4    | 3.1       |
| 40°-50°   | 1.6    | 0.6       |
| 50°-60°   | 0.2    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 265.6  | 96.3      |
| 0°-40°    | 274.0  | 99.3      |
| 0°-60°    | 275.9  | 100.0     |
| 0°-90°    | 276.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 276.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1001 |      |
| 5°  | 985  | 90   |
| 15° | 530  | 140  |
| 25° | 66   | 36   |
| 35° | 12   | 8    |
| 45° | 2    | 2    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1263859

CATALOG NUMBER: P3AS02R309730DE010 E3D1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1001.4 |
| 1°    | 1000.7 |
| 2°    | 998.3  |
| 3°    | 995.6  |
| 4°    | 991.7  |
| 5°    | 984.6  |
| 6°    | 973.1  |
| 7°    | 954.1  |
| 8°    | 928.0  |
| 9°    | 894.1  |
| 10°   | 849.8  |
| 11°   | 797.2  |
| 12°   | 739.8  |
| 13°   | 673.7  |
| 14°   | 604.5  |
| 15°   | 529.8  |
| 16°   | 456.6  |
| 17°   | 386.1  |
| 18°   | 318.5  |
| 19°   | 256.5  |
| 20°   | 204.2  |
| 21°   | 160.7  |
| 22°   | 126.4  |
| 23°   | 100.1  |
| 24°   | 80.1   |
| 25°   | 65.8   |
| 26°   | 54.9   |
| 27°   | 46.6   |
| 28°   | 40.3   |
| 29°   | 34.5   |
| 30°   | 29.2   |
| 32.5° | 18.4   |
| 35°   | 12.5   |
| 37.5° | 7.8    |
| 40°   | 4.5    |
| 42.5° | 3.0    |
| 45°   | 2.0    |
| 47.5° | 1.2    |
| 50°   | 0.5    |
| 52.5° | 0.2    |
| 55°   | 0.2    |
| 57.5° | 0.1    |
| 60°   | 0.1    |
| 62.5° | 0.1    |
| 65°   | 0.1    |



TEST NUMBER: P1263859

CATALOG NUMBER: P3AS02R309730DE010 E3D1WMH

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.1 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)