

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263894

Luminaire Tested: P3AS02R359730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263894
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 87.0 lumens
Efficiency: N/A
Efficacy: 24.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263894
CATALOG NUMBER: P3AS02R359730DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1263894
 CATALOG NUMBER: P3AS02R359730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19867
5°	19458
10°	18214
15°	16345
20°	14235
25°	12122
30°	10153
35°	8084
40°	5840
45°	3690
50°	2013
55°	1415
60°	1316
65°	1245
70°	1154
75°	1017
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3690 cd/sqm



TEST NUMBER: P1263894
 CATALOG NUMBER: P3AS02R359730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.2	9.5
10°-20°	20.0	23.0
20°-30°	23.0	26.4
30°-40°	18.8	21.6
40°-50°	9.4	10.9
50°-60°	3.5	4.0
60°-70°	2.3	2.7
70°-80°	1.3	1.5
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	51.2	58.9
0°-40°	70.0	80.5
0°-60°	82.9	95.3
0°-90°	87.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	87.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	91	
5°	88	8
15°	72	20
25°	50	23
35°	30	19
45°	12	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1263894
CATALOG NUMBER: P3AS02R359730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	90.6
1°	90.5
2°	90.3
3°	89.9
4°	89.2
5°	88.4
6°	87.3
7°	86.2
8°	84.8
9°	83.4
10°	81.8
11°	80.1
12°	78.3
13°	76.2
14°	74.1
15°	72.0
17.5°	66.5
20°	61.0
22.5°	55.3
25°	50.1
27.5°	45.0
30°	40.1
32.5°	35.2
35°	30.2
37.5°	25.3
40°	20.4
42.5°	15.9
45°	11.9
47.5°	8.6
50°	5.9
52.5°	4.3
55°	3.7
57.5°	3.3
60°	3.0
62.5°	2.7
65°	2.4
67.5°	2.0
70°	1.8
72.5°	1.5
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.2



TEST NUMBER: P1263894
CATALOG NUMBER: P3AS02R359730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)