

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263904

Luminaire Tested: P3AS02R359730DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359730DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 230.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263904

CATALOG NUMBER: P3AS02R359730DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1263904

CATALOG NUMBER: P3AS02R359730DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107		112	109	107	106		105	104	102		102	100	99		98	97	96
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85		99	93	88	85		91	87	84		89	85	83		87	84	82
5	96	89	84	80		95	88	83	80		86	82	79		85	81	78		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	77	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	69		84	77	72	69		76	71	68		75	71	68		74	70	68
9	82	74	69	66		81	74	69	65		73	68	65		72	68	65		71	68	65
10	79	71	66	63		78	71	66	63		70	66	63		69	65	62		69	65	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115999
5°	111490
10°	97126
15°	74393
20°	49774
25°	30123
30°	17294
35°	9664
40°	5124
45°	2636
50°	1262
55°	994
60°	965
65°	778
70°	833
75°	763
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2636 cd/sqm

TEST NUMBER: P1263904

CATALOG NUMBER: P3AS02R359730DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	20.0
10°-20°	89.3	38.8
20°-30°	58.5	25.4
30°-40°	23.7	10.3
40°-50°	7.1	3.1
50°-60°	2.4	1.0
60°-70°	1.6	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	193.9	84.3
0°-40°	217.6	94.6
0°-60°	227.1	98.7
0°-90°	230.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	230.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	529	
5°	506	46
15°	328	89
25°	124	58
35°	36	24
45°	8	7
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263904

CATALOG NUMBER: P3AS02R359730DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	529.0
1°	528.1
2°	525.7
3°	520.9
4°	515.2
5°	506.5
6°	495.5
7°	483.3
8°	469.5
9°	453.8
10°	436.2
11°	416.8
12°	396.4
13°	373.7
14°	352.0
15°	327.7
17.5°	268.9
20°	213.3
22.5°	164.1
25°	124.5
27.5°	92.8
30°	68.3
32.5°	50.1
35°	36.1
37.5°	25.6
40°	17.9
42.5°	12.5
45°	8.5
47.5°	5.7
50°	3.7
52.5°	2.8
55°	2.6
57.5°	2.4
60°	2.2
62.5°	2.0
65°	1.5
67.5°	1.3
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.7
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1263904

CATALOG NUMBER: P3AS02R359730DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)