

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264576

Luminaire Tested: P3AS09R159730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 404.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264576

CATALOG NUMBER: P3AS09R159730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264576

CATALOG NUMBER: P3AS09R159730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174218
5°	161017
10°	128544
15°	97095
20°	73950
25°	56350
30°	40361
35°	26341
40°	16145
45°	9768
50°	6482
55°	5008
60°	4298
65°	3736
70°	3334
75°	3304
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9768 cd/sqm

TEST NUMBER: P1264576

CATALOG NUMBER: P3AS09R159730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.8	16.0
10°-20°	119.6	29.6
20°-30°	106.4	26.3
30°-40°	63.0	15.6
40°-50°	25.8	6.4
50°-60°	12.1	3.0
60°-70°	7.4	1.8
70°-80°	3.9	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.8	72.0
0°-40°	353.8	87.6
0°-60°	391.7	97.0
0°-90°	404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	794	
5°	732	65
15°	428	120
25°	233	106
35°	98	63
45°	32	26
55°	13	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1264576

CATALOG NUMBER: P3AS09R159730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	794.5
1°	792.5
2°	786.6
3°	774.8
4°	755.1
5°	731.5
6°	705.9
7°	675.7
8°	644.2
9°	612.1
10°	577.3
12.5°	497.9
15°	427.7
17.5°	367.4
20°	316.9
22.5°	272.3
25°	232.9
27.5°	194.8
30°	159.4
32.5°	127.3
35°	98.4
37.5°	75.4
40°	56.4
42.5°	42.0
45°	31.5
47.5°	24.3
50°	19.0
52.5°	15.7
55°	13.1
57.5°	11.2
60°	9.8
62.5°	8.5
65°	7.2
67.5°	6.6
70°	5.2
72.5°	4.6
75°	3.9
77.5°	2.6
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)