

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264578

Luminaire Tested: P3AS09R159730DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264578
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159730DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 432.0 lumens
Efficiency: N/A
Efficacy: 38.9 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264578

CATALOG NUMBER: P3AS09R159730DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1264578

CATALOG NUMBER: P3AS09R159730DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125714
5°	117851
10°	96636
15°	75074
20°	59272
25°	47229
30°	37905
35°	30945
40°	25505
45°	21460
50°	18422
55°	15942
60°	14122
65°	12297
70°	10963
75°	8811
80°	7198
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21460 cd/sqm

TEST NUMBER: P1264578

CATALOG NUMBER: P3AS09R159730DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	11.1
10°-20°	92.6	21.4
20°-30°	90.0	20.8
30°-40°	72.8	16.8
40°-50°	54.0	12.5
50°-60°	37.8	8.7
60°-70°	23.7	5.5
70°-80°	11.2	2.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.5	53.3
0°-40°	303.3	70.2
0°-60°	395.1	91.4
0°-90°	432.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	432.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	573	
5°	535	48
15°	331	93
25°	195	90
35°	116	73
45°	69	54
55°	42	38
65°	24	24
75°	10	11
85°	2	2
90°	0	

TEST NUMBER: P1264578

CATALOG NUMBER: P3AS09R159730DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	573.3
2.5°	563.8
5°	535.4
7.5°	489.9
10°	434.0
12.5°	379.0
15°	330.7
17.5°	290.0
20°	254.0
22.5°	222.7
25°	195.2
27.5°	170.6
30°	149.7
32.5°	131.7
35°	115.6
37.5°	101.4
40°	89.1
42.5°	78.7
45°	69.2
47.5°	61.6
50°	54.0
52.5°	47.4
55°	41.7
57.5°	37.0
60°	32.2
62.5°	27.5
65°	23.7
67.5°	19.9
70°	17.1
72.5°	13.3
75°	10.4
77.5°	7.6
80°	5.7
82.5°	2.8
85°	1.9
87.5°	0.0
90°	0.0

(END OF REPORT)