

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263954

Luminaire Tested: P3AS02R459730DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1263954  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R459730DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 190.0 lumens  
Efficiency: N/A  
Efficacy: 52.8 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263954  
CATALOG NUMBER: P3AS02R459730DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1263954  
 CATALOG NUMBER: P3AS02R459730DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	40282
5°	39577
10°	37452
15°	34143
20°	30196
25°	26227
30°	22510
35°	18765
40°	13969
45°	8559
50°	3957
55°	3097
60°	2982
65°	2750
70°	2500
75°	2372
80°	2273
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8559 cd/sqm



TEST NUMBER: P1263954  
 CATALOG NUMBER: P3AS02R459730DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	16.8	8.8
10°-20°	41.9	22.0
20°-30°	49.8	26.2
30°-40°	43.2	22.8
40°-50°	21.7	11.4
50°-60°	7.5	4.0
60°-70°	5.3	2.8
70°-80°	2.9	1.5
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.4	57.1
0°-40°	151.7	79.8
0°-60°	180.9	95.2
0°-90°	190.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	190.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	184	
5°	180	17
15°	150	42
25°	108	50
35°	70	43
45°	28	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1263954  
CATALOG NUMBER: P3AS02R459730DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	183.7
2.5°	182.8
5°	179.8
7.5°	175.0
10°	168.2
12.5°	159.8
15°	150.4
17.5°	139.9
20°	129.4
22.5°	118.7
25°	108.4
27.5°	98.5
30°	88.9
32.5°	79.7
35°	70.1
37.5°	59.8
40°	48.8
42.5°	38.1
45°	27.6
47.5°	18.2
50°	11.6
52.5°	9.0
55°	8.1
57.5°	7.4
60°	6.8
62.5°	6.1
65°	5.3
67.5°	4.6
70°	3.9
72.5°	3.3
75°	2.8
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)