

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263985

Luminaire Tested: P3AS02R509730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 191.0 lumens
Efficiency: N/A
Efficacy: 53.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263985
CATALOG NUMBER: P3AS02R509730DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1263985
 CATALOG NUMBER: P3AS02R509730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38813
5°	38235
10°	36539
15°	33848
20°	30429
25°	26735
30°	22738
35°	18444
40°	13855
45°	8931
50°	4230
55°	3326
60°	3158
65°	2958
70°	2629
75°	2372
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8931 cd/sqm



TEST NUMBER: P1263985

CATALOG NUMBER: P3AS02R509730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.3	8.5
10°-20°	41.6	21.8
20°-30°	50.5	26.4
30°-40°	42.8	22.4
40°-50°	22.3	11.7
50°-60°	8.0	4.2
60°-70°	5.6	2.9
70°-80°	3.0	1.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.4	56.7
0°-40°	151.2	79.2
0°-60°	181.5	95.0
0°-90°	191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	191.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	177	
5°	174	16
15°	149	42
25°	110	51
35°	69	43
45°	29	22
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1263985
CATALOG NUMBER: P3AS02R509730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	177.0
2.5°	176.4
5°	173.7
7.5°	169.8
10°	164.1
12.5°	157.0
15°	149.1
17.5°	140.2
20°	130.4
22.5°	120.3
25°	110.5
27.5°	100.3
30°	89.8
32.5°	79.3
35°	68.9
37.5°	58.6
40°	48.4
42.5°	38.6
45°	28.8
47.5°	19.2
50°	12.4
52.5°	9.6
55°	8.7
57.5°	7.8
60°	7.2
62.5°	6.3
65°	5.7
67.5°	4.8
70°	4.1
72.5°	3.5
75°	2.8
77.5°	2.2
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)