

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264661

Luminaire Tested: P3AS09R309730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 18.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264661

CATALOG NUMBER: P3AS09R309730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264661

CATALOG NUMBER: P3AS09R309730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		68	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70740
5°	68523
10°	61745
15°	51079
20°	39553
25°	29663
30°	21548
35°	14348
40°	8817
45°	5179
50°	3173
55°	2561
60°	2237
65°	1816
70°	1667
75°	1610
80°	1263
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5179 cd/sqm

TEST NUMBER: P1264661

CATALOG NUMBER: P3AS09R309730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.6	13.8
10°-20°	62.0	29.9
20°-30°	56.4	27.2
30°-40°	34.1	16.5
40°-50°	13.7	6.6
50°-60°	6.0	2.9
60°-70°	3.6	1.8
70°-80°	2.0	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	147.0	71.0
0°-40°	181.1	87.5
0°-60°	200.8	97.0
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	323	
5°	311	29
15°	225	62
25°	123	56
35°	54	34
45°	17	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1264661

CATALOG NUMBER: P3AS09R309730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	322.6
1°	322.3
2°	321.0
3°	318.7
4°	315.5
5°	311.3
6°	306.2
7°	300.8
8°	293.7
9°	285.7
10°	277.3
11°	267.7
12°	257.4
13°	247.2
14°	235.9
15°	225.0
17.5°	196.4
20°	169.5
22.5°	144.4
25°	122.6
27.5°	102.7
30°	85.1
32.5°	68.7
35°	53.6
37.5°	41.1
40°	30.8
42.5°	22.5
45°	16.7
47.5°	12.5
50°	9.3
52.5°	7.4
55°	6.7
57.5°	5.8
60°	5.1
62.5°	4.2
65°	3.5
67.5°	3.2
70°	2.6
72.5°	2.2
75°	1.9
77.5°	1.6
80°	1.0
82.5°	0.6
85°	0.6
87.5°	0.3



TEST NUMBER: P1264661

CATALOG NUMBER: P3AS09R309730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)