

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264078

Luminaire Tested: P3AS02R659730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 151.0 lumens
Efficiency: N/A
Efficacy: 42.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264078

CATALOG NUMBER: P3AS02R659730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264078

CATALOG NUMBER: P3AS02R659730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		78
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		62
7	81	71	65	60	79	70	64	60	69	63	60		68	63	59		57
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38374
5°	37420
10°	34847
15°	31237
20°	26976
25°	22429
30°	17699
35°	13117
40°	9046
45°	5613
50°	3036
55°	1912
60°	1623
65°	1453
70°	1282
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5613 cd/sqm

TEST NUMBER: P1264078

CATALOG NUMBER: P3AS02R659730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.8	10.5
10°-20°	38.2	25.3
20°-30°	42.3	28.0
30°-40°	30.7	20.3
40°-50°	14.4	9.5
50°-60°	4.9	3.2
60°-70°	2.8	1.9
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	96.3	63.8
0°-40°	127.0	84.1
0°-60°	146.3	96.9
0°-90°	151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	175	
5°	170	16
15°	138	38
25°	93	42
35°	49	31
45°	18	14
55°	5	5
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264078

CATALOG NUMBER: P3AS02R659730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	175.0
2.5°	173.9
5°	170.0
7.5°	164.1
10°	156.5
12.5°	147.6
15°	137.6
17.5°	126.7
20°	115.6
22.5°	104.1
25°	92.7
27.5°	81.2
30°	69.9
32.5°	59.0
35°	49.0
37.5°	39.8
40°	31.6
42.5°	24.2
45°	18.1
47.5°	13.1
50°	8.9
52.5°	6.1
55°	5.0
57.5°	4.4
60°	3.7
62.5°	3.3
65°	2.8
67.5°	2.4
70°	2.0
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)