

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264080

Luminaire Tested: P3AS02R709730DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709730DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264080

CATALOG NUMBER: P3AS02R709730DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1264080

CATALOG NUMBER: P3AS02R709730DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54206
5°	51728
10°	49209
15°	47900
20°	46134
25°	43672
30°	40614
35°	34104
40°	21984
45°	10203
50°	2695
55°	650
60°	658
65°	571
70°	577
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10203 cd/sqm

TEST NUMBER: P1264080

CATALOG NUMBER: P3AS02R709730DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.0	8.1
10°-20°	59.3	21.7
20°-30°	82.8	30.3
30°-40°	76.8	28.1
40°-50°	27.5	10.1
50°-60°	2.3	0.8
60°-70°	1.2	0.4
70°-80°	0.8	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.1	60.1
0°-40°	240.9	88.3
0°-60°	270.8	99.2
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	247	
5°	235	22
15°	211	59
25°	180	83
35°	127	77
45°	33	28
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264080

CATALOG NUMBER: P3AS02R709730DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	247.2
2.5°	243.5
5°	235.0
7.5°	227.1
10°	221.0
12.5°	216.0
15°	211.0
17.5°	204.9
20°	197.7
22.5°	189.4
25°	180.5
27.5°	171.3
30°	160.4
32.5°	146.4
35°	127.4
37.5°	103.2
40°	76.8
42.5°	52.4
45°	32.9
47.5°	18.3
50°	7.9
52.5°	2.6
55°	1.7
57.5°	1.5
60°	1.5
62.5°	1.3
65°	1.1
67.5°	1.1
70°	0.9
72.5°	0.9
75°	0.7
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)