

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264096

Luminaire Tested: P3AS02R709730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 77.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264096

CATALOG NUMBER: P3AS02R709730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264096

CATALOG NUMBER: P3AS02R709730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	63	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18069
5°	17720
10°	16722
15°	15165
20°	13278
25°	11202
30°	9166
35°	7121
40°	5095
45°	3225
50°	1603
55°	994
60°	833
65°	778
70°	705
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3225 cd/sqm

TEST NUMBER: P1264096

CATALOG NUMBER: P3AS02R709730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.5	9.8
10°-20°	18.6	24.2
20°-30°	21.2	27.5
30°-40°	16.6	21.5
40°-50°	8.1	10.6
50°-60°	2.5	3.2
60°-70°	1.5	1.9
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	47.3	61.4
0°-40°	63.9	83.0
0°-60°	74.5	96.8
0°-90°	77.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	77.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	82	
5°	80	8
15°	67	19
25°	46	21
35°	27	17
45°	10	8
55°	3	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264096

CATALOG NUMBER: P3AS02R709730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	82.4
2.5°	81.9
5°	80.5
7.5°	78.3
10°	75.1
12.5°	71.3
15°	66.8
17.5°	62.0
20°	56.9
22.5°	51.5
25°	46.3
27.5°	41.1
30°	36.2
32.5°	31.3
35°	26.6
37.5°	22.1
40°	17.8
42.5°	13.8
45°	10.4
47.5°	7.3
50°	4.7
52.5°	3.1
55°	2.6
57.5°	2.2
60°	1.9
62.5°	1.7
65°	1.5
67.5°	1.3
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.6
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)