

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264133

Luminaire Tested: P3AS05R109730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264133
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 237.0 lumens
Efficiency: N/A
Efficacy: 30.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264133

CATALOG NUMBER: P3AS05R109730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264133

CATALOG NUMBER: P3AS05R109730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		93
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		86
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		80
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		75
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		70
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		66
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		62
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102207
5°	94453
10°	75416
15°	56958
20°	43380
25°	33050
30°	23675
35°	15446
40°	9475
45°	5737
50°	3821
55°	2944
60°	2544
65°	2179
70°	1988
75°	1949
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5737 cd/sqm

TEST NUMBER: P1264133

CATALOG NUMBER: P3AS05R109730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.0	16.0
10°-20°	70.1	29.6
20°-30°	62.4	26.3
30°-40°	36.9	15.6
40°-50°	15.2	6.4
50°-60°	7.1	3.0
60°-70°	4.3	1.8
70°-80°	2.3	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	170.6	72.0
0°-40°	207.5	87.6
0°-60°	229.8	97.0
0°-90°	237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	237.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	466	
5°	429	38
15°	251	70
25°	137	62
35°	58	37
45°	18	15
55°	8	7
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1264133

CATALOG NUMBER: P3AS05R109730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	466.1
1°	464.9
2°	461.4
3°	454.5
4°	443.0
5°	429.1
6°	414.1
7°	396.4
8°	377.9
9°	359.1
10°	338.7
12.5°	292.1
15°	250.9
17.5°	215.5
20°	185.9
22.5°	159.7
25°	136.6
27.5°	114.3
30°	93.5
32.5°	74.7
35°	57.7
37.5°	44.3
40°	33.1
42.5°	24.6
45°	18.5
47.5°	14.2
50°	11.2
52.5°	9.2
55°	7.7
57.5°	6.5
60°	5.8
62.5°	5.0
65°	4.2
67.5°	3.8
70°	3.1
72.5°	2.7
75°	2.3
77.5°	1.5
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)