

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264721

Luminaire Tested: P3AS09R409730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 236.0 lumens
Efficiency: N/A
Efficacy: 21.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264721

CATALOG NUMBER: P3AS09R409730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264721

CATALOG NUMBER: P3AS09R409730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73481
5°	72001
10°	67044
15°	58434
20°	47091
25°	35300
30°	24814
35°	16249
40°	9847
45°	5892
50°	3514
55°	2829
60°	2544
65°	2179
70°	2052
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5892 cd/sqm

TEST NUMBER: P1264721

CATALOG NUMBER: P3AS09R409730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.4	12.9
10°-20°	70.9	30.0
20°-30°	66.8	28.3
30°-40°	38.6	16.4
40°-50°	15.4	6.5
50°-60°	6.8	2.9
60°-70°	4.2	1.8
70°-80°	2.2	0.9
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.1	71.2
0°-40°	206.7	87.6
0°-60°	228.9	97.0
0°-90°	236.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	236.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	335	
5°	327	30
15°	257	71
25°	146	67
35°	61	39
45°	19	15
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1264721

CATALOG NUMBER: P3AS09R409730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	335.1
2.5°	333.2
5°	327.1
7.5°	315.8
10°	301.1
12.5°	281.1
15°	257.4
17.5°	230.7
20°	201.8
22.5°	172.9
25°	145.9
27.5°	120.8
30°	98.0
32.5°	78.1
35°	60.7
37.5°	45.9
40°	34.4
42.5°	25.7
45°	19.0
47.5°	13.8
50°	10.3
52.5°	8.4
55°	7.4
57.5°	6.7
60°	5.8
62.5°	4.8
65°	4.2
67.5°	3.5
70°	3.2
72.5°	2.6
75°	1.9
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)