

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264136

Luminaire Tested: P3AS05R109730DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109730DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 210.1 lumens
Efficiency: N/A
Efficacy: 26.6 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264136

CATALOG NUMBER: P3AS05R109730DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1264136

CATALOG NUMBER: P3AS05R109730DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	92	92	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	83	83	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	76	76	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	70	70	68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	65	65	63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	60	60	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	57	57	55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	53	53	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	50	50	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	48	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78590
5°	72177
10°	57514
15°	42974
20°	32646
25°	24703
30°	18281
35°	13063
40°	8931
45°	6264
50°	5322
55°	5238
60°	5438
65°	5759
70°	5834
75°	6100
80°	6566
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 7728 cd/sqm

TEST NUMBER: P1264136

CATALOG NUMBER: P3AS05R109730DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	13.8
10°-20°	53.1	25.3
20°-30°	47.0	22.4
30°-40°	30.8	14.7
40°-50°	16.5	7.8
50°-60°	12.5	5.9
60°-70°	10.7	5.1
70°-80°	7.4	3.5
80°-90°	3.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	129.2	61.5
0°-40°	160.0	76.2
0°-60°	188.9	89.9
0°-90°	210.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	210.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	358	
5°	328	29
15°	189	53
25°	102	47
35°	49	31
45°	20	16
55°	14	12
65°	11	11
75°	7	7
85°	3	3
90°	0	

TEST NUMBER: P1264136

CATALOG NUMBER: P3AS05R109730DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	358.4
2.5°	350.0
5°	327.9
7.5°	295.3
10°	258.3
12.5°	222.5
15°	189.3
17.5°	162.6
20°	139.9
22.5°	119.7
25°	102.1
27.5°	86.5
30°	72.2
32.5°	59.8
35°	48.8
37.5°	39.0
40°	31.2
42.5°	24.7
45°	20.2
47.5°	17.6
50°	15.6
52.5°	15.0
55°	13.7
57.5°	13.0
60°	12.4
62.5°	11.7
65°	11.1
67.5°	9.8
70°	9.1
72.5°	7.8
75°	7.2
77.5°	5.9
80°	5.2
82.5°	4.6
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)