

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264164

Luminaire Tested: P3AS05R129730DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264164
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129730DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 267.0 lumens
Efficiency: N/A
Efficacy: 35.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264164

CATALOG NUMBER: P3AS05R129730DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1264164

CATALOG NUMBER: P3AS05R129730DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	73		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		68	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115144
5°	106405
10°	84946
15°	64177
20°	48864
25°	37236
30°	26688
35°	17400
40°	10677
45°	6450
50°	4298
55°	3326
60°	2851
65°	2491
70°	2244
75°	2203
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6450 cd/sqm

TEST NUMBER: P1264164

CATALOG NUMBER: P3AS05R129730DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	16.0
10°-20°	79.0	29.6
20°-30°	70.3	26.3
30°-40°	41.6	15.6
40°-50°	17.1	6.4
50°-60°	8.0	3.0
60°-70°	4.9	1.8
70°-80°	2.6	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.2	72.0
0°-40°	233.8	87.6
0°-60°	258.9	97.0
0°-90°	267.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	267.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	525	
5°	483	43
15°	283	79
25°	154	70
35°	65	42
45°	21	17
55°	9	8
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1264164

CATALOG NUMBER: P3AS05R129730DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	525.1
1°	523.8
2°	519.9
3°	512.1
4°	499.0
5°	483.4
6°	466.5
7°	446.6
8°	425.8
9°	404.5
10°	381.5
12.5°	329.1
15°	282.7
17.5°	242.8
20°	209.4
22.5°	179.9
25°	153.9
27.5°	128.8
30°	105.4
32.5°	84.1
35°	65.0
37.5°	49.9
40°	37.3
42.5°	27.7
45°	20.8
47.5°	16.0
50°	12.6
52.5°	10.4
55°	8.7
57.5°	7.4
60°	6.5
62.5°	5.6
65°	4.8
67.5°	4.3
70°	3.5
72.5°	3.0
75°	2.6
77.5°	1.7
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)