

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264725

Luminaire Tested: P3AS09R409730DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R409730DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 764.0 lumens  
Efficiency: N/A  
Efficacy: 68.8 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264725  
CATALOG NUMBER: P3AS09R409730DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1264725  
 CATALOG NUMBER: P3AS09R409730DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94	94	94	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63	63	63	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60	60	60	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	338065
5°	328240
10°	297879
15°	246085
20°	177512
25°	109797
30°	59452
35°	30731
40°	16717
45°	9365
50°	4708
55°	3517
60°	3158
65°	3061
70°	2949
75°	2796
80°	2526
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9365 cd/sqm



TEST NUMBER: P1264725  
 CATALOG NUMBER: P3AS09R409730DE010 E3DLP1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.5	18.0
10°-20°	295.2	38.6
20°-30°	210.6	27.6
30°-40°	77.6	10.2
40°-50°	24.4	3.2
50°-60°	8.5	1.1
60°-70°	5.8	0.8
70°-80°	3.5	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	643.3	84.2
0°-40°	720.8	94.3
0°-60°	753.7	98.7
0°-90°	764.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	764.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1542	
5°	1491	137
15°	1084	295
25°	454	211
35°	115	78
45°	30	24
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1264725  
CATALOG NUMBER: P3AS09R409730DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1541.7
2.5°	1529.9
5°	1491.2
7.5°	1426.9
10°	1337.8
12.5°	1224.3
15°	1084.0
17.5°	926.6
20°	760.7
22.5°	597.4
25°	453.8
27.5°	333.1
30°	234.8
32.5°	164.6
35°	114.8
37.5°	81.3
40°	58.4
42.5°	42.0
45°	30.2
47.5°	20.3
50°	13.8
52.5°	9.8
55°	9.2
57.5°	8.5
60°	7.2
62.5°	6.6
65°	5.9
67.5°	5.2
70°	4.6
72.5°	3.9
75°	3.3
77.5°	2.6
80°	2.0
82.5°	1.3
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)