

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264747

Luminaire Tested: P3AS09R459730DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459730DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 473.0 lumens
Efficiency: N/A
Efficacy: 42.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264747

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1264747

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74		
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69		
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64		
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56		
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53		
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140888
5°	137684
10°	127007
15°	110443
20°	90728
25°	70577
30°	52135
35°	36674
40°	22900
45°	12404
50°	6720
55°	5773
60°	5175
65°	4410
70°	3783
75°	3897
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12404 cd/sqm

TEST NUMBER: P1264747

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	12.2
10°-20°	134.5	28.4
20°-30°	133.5	28.2
30°-40°	86.0	18.2
40°-50°	33.1	7.0
50°-60°	13.5	2.8
60°-70°	8.5	1.8
70°-80°	4.6	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.9	68.9
0°-40°	411.9	87.1
0°-60°	458.5	96.9
0°-90°	473.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	473.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	642	
5°	626	58
15°	486	134
25°	292	134
35°	137	86
45°	40	33
55°	15	13
65°	8	8
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1264747

CATALOG NUMBER: P3AS09R459730DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	642.5
2.5°	639.2
5°	625.5
7.5°	601.9
10°	570.4
12.5°	531.0
15°	486.5
17.5°	437.9
20°	388.8
22.5°	339.0
25°	291.7
27.5°	247.2
30°	205.9
32.5°	169.8
35°	137.0
37.5°	107.5
40°	80.0
42.5°	57.7
45°	40.0
47.5°	26.9
50°	19.7
52.5°	16.4
55°	15.1
57.5°	13.1
60°	11.8
62.5°	9.8
65°	8.5
67.5°	7.2
70°	5.9
72.5°	5.2
75°	4.6
77.5°	3.3
80°	2.6
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)