

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264181

Luminaire Tested: P3AS05R159730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 228.0 lumens
Efficiency: N/A
Efficacy: 31.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264181

CATALOG NUMBER: P3AS05R159730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264181

CATALOG NUMBER: P3AS05R159730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	86	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	76	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194765
5°	172881
10°	120060
15°	71011
20°	40440
25°	23106
30°	12787
35°	6826
40°	3779
45°	2047
50°	1262
55°	994
60°	877
65°	778
70°	705
75°	763
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2047 cd/sqm

TEST NUMBER: P1264181

CATALOG NUMBER: P3AS05R159730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	29.3
10°-20°	88.1	38.7
20°-30°	45.4	19.9
30°-40°	17.0	7.5
40°-50°	5.6	2.4
50°-60°	2.4	1.1
60°-70°	1.5	0.7
70°-80°	0.9	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	200.3	87.9
0°-40°	217.4	95.3
0°-60°	225.3	98.8
0°-90°	228.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	228.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	888	
5°	785	67
15°	313	88
25°	96	45
35°	26	17
45°	7	6
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264181

CATALOG NUMBER: P3AS05R159730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	888.2
1°	886.5
2°	874.8
3°	852.6
4°	823.4
5°	785.4
6°	742.4
7°	695.2
8°	642.7
9°	590.8
10°	539.2
12.5°	414.9
15°	312.8
17.5°	234.1
20°	173.3
22.5°	129.4
25°	95.5
27.5°	69.6
30°	50.5
32.5°	35.8
35°	25.5
37.5°	18.2
40°	13.2
42.5°	9.4
45°	6.6
47.5°	4.8
50°	3.7
52.5°	3.1
55°	2.6
57.5°	2.2
60°	2.0
62.5°	1.8
65°	1.5
67.5°	1.3
70°	1.1
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)