

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264792

Luminaire Tested: P3AS09R559730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 351.0 lumens
Efficiency: N/A
Efficacy: 31.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264792

CATALOG NUMBER: P3AS09R559730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264792

CATALOG NUMBER: P3AS09R559730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96374
5°	95399
10°	92138
15°	85154
20°	73483
25°	58044
30°	41171
35°	26555
40°	15944
45°	8993
50°	4844
55°	1720
60°	1535
65°	1505
70°	1475
75°	1356
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8993 cd/sqm

TEST NUMBER: P1264792

CATALOG NUMBER: P3AS09R559730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	11.6
10°-20°	103.7	29.6
20°-30°	108.7	31.0
30°-40°	63.4	18.1
40°-50°	23.7	6.8
50°-60°	5.6	1.6
60°-70°	2.9	0.8
70°-80°	1.7	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	253.2	72.1
0°-40°	316.6	90.2
0°-60°	345.9	98.6
0°-90°	351.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	351.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	440	
5°	433	41
15°	375	104
25°	240	109
35°	99	63
45°	29	24
55°	4	6
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1264792

CATALOG NUMBER: P3AS09R559730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	439.5
2.5°	438.2
5°	433.4
7.5°	425.7
10°	413.8
12.5°	397.0
15°	375.1
17.5°	347.4
20°	314.9
22.5°	278.5
25°	239.9
27.5°	200.3
30°	162.6
32.5°	128.5
35°	99.2
37.5°	75.3
40°	55.7
42.5°	39.9
45°	29.0
47.5°	20.9
50°	14.2
52.5°	8.1
55°	4.5
57.5°	3.9
60°	3.5
62.5°	3.2
65°	2.9
67.5°	2.6
70°	2.3
72.5°	1.9
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)