

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264806

Luminaire Tested: P3AS09R559730DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559730DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 477.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264806

CATALOG NUMBER: P3AS09R559730DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264806

CATALOG NUMBER: P3AS09R559730DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80	79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129748
5°	126502
10°	117611
15°	104723
20°	89001
25°	71835
30°	54768
35°	38949
40°	25705
45°	15226
50°	8938
55°	5505
60°	4868
65°	4410
70°	3783
75°	3304
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15226 cd/sqm

TEST NUMBER: P1264806

CATALOG NUMBER: P3AS09R559730DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	11.2
10°-20°	127.9	26.8
20°-30°	135.5	28.4
30°-40°	91.5	19.2
40°-50°	40.1	8.4
50°-60°	14.3	3.0
60°-70°	8.4	1.8
70°-80°	4.4	0.9
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.7	66.4
0°-40°	408.3	85.6
0°-60°	462.7	97.0
0°-90°	477.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	477.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	592	
5°	575	53
15°	461	128
25°	297	135
35°	146	92
45°	49	40
55°	14	14
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1264806

CATALOG NUMBER: P3AS09R559730DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	591.7
2.5°	587.2
5°	574.7
7.5°	554.4
10°	528.2
12.5°	496.7
15°	461.3
17.5°	422.0
20°	381.4
22.5°	338.8
25°	296.9
27.5°	255.6
30°	216.3
32.5°	178.9
35°	145.5
37.5°	115.3
40°	89.8
42.5°	67.5
45°	49.1
47.5°	36.0
50°	26.2
52.5°	18.3
55°	14.4
57.5°	13.1
60°	11.1
62.5°	9.8
65°	8.5
67.5°	7.2
70°	5.9
72.5°	5.2
75°	3.9
77.5°	3.3
80°	2.6
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)