

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264821

Luminaire Tested: P3AS09R609730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 338.0 lumens
Efficiency: N/A
Efficacy: 30.5 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264821

CATALOG NUMBER: P3AS09R609730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264821

CATALOG NUMBER: P3AS09R609730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79818
5°	79066
10°	76752
15°	71919
20°	63636
25°	53253
30°	41728
35°	30276
40°	20152
45°	12559
50°	6789
55°	1950
60°	1842
65°	1660
70°	1667
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12559 cd/sqm

TEST NUMBER: P1264821

CATALOG NUMBER: P3AS09R609730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	10.0
10°-20°	87.9	26.0
20°-30°	100.2	29.6
30°-40°	71.0	21.0
40°-50°	32.2	9.5
50°-60°	6.8	2.0
60°-70°	3.3	1.0
70°-80°	2.0	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.9	65.6
0°-40°	292.9	86.7
0°-60°	332.0	98.2
0°-90°	338.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	338.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	364	
5°	359	34
15°	317	88
25°	220	100
35°	113	71
45°	40	32
55°	5	7
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1264821

CATALOG NUMBER: P3AS09R609730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	364.0
2.5°	362.7
5°	359.2
7.5°	353.1
10°	344.7
12.5°	332.8
15°	316.8
17.5°	296.5
20°	272.7
22.5°	247.0
25°	220.1
27.5°	192.4
30°	164.8
32.5°	138.5
35°	113.1
37.5°	90.6
40°	70.4
42.5°	53.3
45°	40.5
47.5°	30.2
50°	19.9
52.5°	9.3
55°	5.1
57.5°	4.5
60°	4.2
62.5°	3.9
65°	3.2
67.5°	2.9
70°	2.6
72.5°	2.2
75°	1.9
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)