

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264227

Luminaire Tested: P3AS05R209730DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209730DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 220.0 lumens
Efficiency: N/A
Efficacy: 30.6 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264227
CATALOG NUMBER: P3AS05R209730DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1264227

CATALOG NUMBER: P3AS05R209730DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90			90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68			68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63			63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55			55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	59	52	48	68	58	52	48	57	52	48	56	52	48	56	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78239
5°	72969
10°	60564
15°	46311
20°	34746
25°	26155
30°	19345
35°	13518
40°	9275
45°	6419
50°	5526
55°	5429
60°	5701
65°	5707
70°	5834
75°	6015
80°	6566
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 7560 cd/sqm



TEST NUMBER: P1264227

CATALOG NUMBER: P3AS05R209730DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.7	13.5
10°-20°	56.7	25.8
20°-30°	49.9	22.7
30°-40°	32.2	14.6
40°-50°	17.1	7.8
50°-60°	12.8	5.8
60°-70°	10.9	5.0
70°-80°	7.7	3.5
80°-90°	3.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	136.3	62.0
0°-40°	168.5	76.6
0°-60°	198.4	90.2
0°-90°	220.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	220.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	357	
5°	332	30
15°	204	57
25°	108	50
35°	50	32
45°	21	17
55°	14	13
65°	11	11
75°	7	8
85°	3	3
90°	0	



TEST NUMBER: P1264227
CATALOG NUMBER: P3AS05R209730DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	356.8
2.5°	349.7
5°	331.5
7.5°	303.7
10°	272.0
12.5°	237.0
15°	204.0
17.5°	174.2
20°	148.9
22.5°	127.6
25°	108.1
27.5°	91.3
30°	76.4
32.5°	62.8
35°	50.5
37.5°	40.8
40°	32.4
42.5°	25.9
45°	20.7
47.5°	18.1
50°	16.2
52.5°	14.9
55°	14.2
57.5°	13.6
60°	13.0
62.5°	11.7
65°	11.0
67.5°	10.4
70°	9.1
72.5°	8.4
75°	7.1
77.5°	6.5
80°	5.2
82.5°	4.5
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)