

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264239

Luminaire Tested: P3AS05R259730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 230.0 lumens
Efficiency: N/A
Efficacy: 31.9 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264239

CATALOG NUMBER: P3AS05R259730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264239

CATALOG NUMBER: P3AS05R259730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147532
5°	137640
10°	110263
15°	74847
20°	45294
25°	26493
30°	15091
35°	8298
40°	4408
45°	2326
50°	1365
55°	994
60°	877
65°	934
70°	833
75°	763
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2326 cd/sqm

TEST NUMBER: P1264239

CATALOG NUMBER: P3AS05R259730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.5	24.1
10°-20°	90.6	39.4
20°-30°	51.8	22.5
30°-40°	20.4	8.9
40°-50°	6.3	2.7
50°-60°	2.5	1.1
60°-70°	1.7	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	197.9	86.0
0°-40°	218.4	94.9
0°-60°	227.1	98.7
0°-90°	230.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	230.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	673	
5°	625	55
15°	330	91
25°	110	52
35°	31	20
45°	8	6
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264239

CATALOG NUMBER: P3AS05R259730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	672.8
1°	671.5
2°	666.0
3°	656.3
4°	642.9
5°	625.3
6°	604.7
7°	581.4
8°	554.3
9°	526.7
10°	495.2
11°	464.2
12°	430.2
13°	396.5
14°	362.0
15°	329.7
17.5°	255.6
20°	194.1
22.5°	145.7
25°	109.5
27.5°	81.1
30°	59.6
32.5°	43.1
35°	31.0
37.5°	22.0
40°	15.4
42.5°	10.6
45°	7.5
47.5°	5.3
50°	4.0
52.5°	3.1
55°	2.6
57.5°	2.4
60°	2.0
62.5°	1.8
65°	1.8
67.5°	1.5
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1264239

CATALOG NUMBER: P3AS05R259730DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)