

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264245

Luminaire Tested: P3AS05R259730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264245
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 177.0 lumens
Efficiency: N/A
Efficacy: 24.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264245

CATALOG NUMBER: P3AS05R259730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264245

CATALOG NUMBER: P3AS05R259730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42058
5°	41052
10°	38053
15°	33893
20°	29123
25°	24751
30°	20383
35°	15874
40°	11421
45°	7257
50°	4298
55°	2944
60°	2719
65°	2542
70°	2244
75°	2033
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7257 cd/sqm

TEST NUMBER: P1264245

CATALOG NUMBER: P3AS05R259730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.3	9.8
10°-20°	41.4	23.4
20°-30°	46.8	26.4
30°-40°	37.0	20.9
40°-50°	18.7	10.6
50°-60°	7.5	4.2
60°-70°	4.8	2.7
70°-80°	2.6	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	105.6	59.6
0°-40°	142.6	80.6
0°-60°	168.8	95.4
0°-90°	177.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	177.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	192	
5°	186	17
15°	149	41
25°	102	47
35°	59	37
45°	23	19
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1264245

CATALOG NUMBER: P3AS05R259730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	191.8
1°	191.8
2°	191.2
3°	190.1
4°	188.5
5°	186.5
6°	184.1
7°	181.3
8°	178.2
9°	174.6
10°	170.9
11°	166.7
12°	162.7
13°	158.1
14°	153.7
15°	149.3
17.5°	136.9
20°	124.8
22.5°	113.3
25°	102.3
27.5°	91.5
30°	80.5
32.5°	70.1
35°	59.3
37.5°	49.4
40°	39.9
42.5°	31.1
45°	23.4
47.5°	17.4
50°	12.6
52.5°	9.5
55°	7.7
57.5°	7.1
60°	6.2
62.5°	5.5
65°	4.9
67.5°	4.2
70°	3.5
72.5°	3.1
75°	2.4
77.5°	2.0
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.2



TEST NUMBER: P1264245

CATALOG NUMBER: P3AS05R259730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)