

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264856

Luminaire Tested: P3AS09R659730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 253.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264856

CATALOG NUMBER: P3AS09R659730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264856

CATALOG NUMBER: P3AS09R659730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45018
5°	44420
10°	42930
15°	40477
20°	37337
25°	33897
30°	30030
35°	25538
40°	20324
45°	14358
50°	8324
55°	4549
60°	4210
65°	3840
70°	3526
75°	3304
80°	2778
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14358 cd/sqm

TEST NUMBER: P1264856

CATALOG NUMBER: P3AS09R659730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.0	7.5
10°-20°	49.9	19.7
20°-30°	64.1	25.3
30°-40°	59.3	23.4
40°-50°	35.8	14.2
50°-60°	12.2	4.8
60°-70°	7.4	2.9
70°-80°	4.2	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	133.0	52.6
0°-40°	192.3	76.0
0°-60°	240.3	95.0
0°-90°	253.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	253.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	205	
5°	202	19
15°	178	50
25°	140	64
35°	95	59
45°	46	36
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1264856

CATALOG NUMBER: P3AS09R659730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	205.3
2.5°	204.4
5°	201.8
7.5°	197.9
10°	192.8
12.5°	186.4
15°	178.3
17.5°	169.7
20°	160.0
22.5°	150.1
25°	140.1
27.5°	129.5
30°	118.6
32.5°	107.6
35°	95.4
37.5°	83.5
40°	71.0
42.5°	58.5
45°	46.3
47.5°	35.0
50°	24.4
52.5°	15.4
55°	11.9
57.5°	10.6
60°	9.6
62.5°	8.4
65°	7.4
67.5°	6.4
70°	5.5
72.5°	4.8
75°	3.9
77.5°	3.2
80°	2.2
82.5°	1.6
85°	1.0
87.5°	0.6
90°	0.0

(END OF REPORT)