

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264271

Luminaire Tested: P3AS05R309730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 233.0 lumens
Efficiency: N/A
Efficacy: 32.4 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264271

CATALOG NUMBER: P3AS05R309730DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1264271

CATALOG NUMBER: P3AS05R309730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90		
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86		
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82		
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78		
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75		
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71		
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69		
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135954
5°	129408
10°	108860
15°	78502
20°	48701
25°	27703
30°	15369
35°	8379
40°	4408
45°	2388
50°	1262
55°	841
60°	789
65°	778
70°	705
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2388 cd/sqm

TEST NUMBER: P1264271

CATALOG NUMBER: P3AS05R309730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	22.7
10°-20°	94.1	40.4
20°-30°	54.4	23.3
30°-40°	20.6	8.9
40°-50°	6.3	2.7
50°-60°	2.1	0.9
60°-70°	1.4	0.6
70°-80°	0.8	0.3
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	201.4	86.5
0°-40°	222.1	95.3
0°-60°	230.5	99.0
0°-90°	233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	620	
5°	588	53
15°	346	94
25°	114	54
35°	31	21
45°	8	6
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264271

CATALOG NUMBER: P3AS05R309730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	620.0
1°	619.6
2°	615.9
3°	608.8
4°	600.0
5°	587.9
6°	572.5
7°	555.3
8°	536.2
9°	513.3
10°	488.9
11°	462.4
12°	434.5
13°	405.2
14°	375.5
15°	345.8
17.5°	272.7
20°	208.7
22.5°	154.7
25°	114.5
27.5°	83.2
30°	60.7
32.5°	43.8
35°	31.3
37.5°	21.8
40°	15.4
42.5°	10.8
45°	7.7
47.5°	5.3
50°	3.7
52.5°	2.6
55°	2.2
57.5°	2.0
60°	1.8
62.5°	1.5
65°	1.5
67.5°	1.3
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0



TEST NUMBER: P1264271

CATALOG NUMBER: P3AS05R309730DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)