

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264918

Luminaire Tested: P3AS10R129730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS10R129730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 490.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264918

CATALOG NUMBER: P3AS10R129730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264918

CATALOG NUMBER: P3AS10R129730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123587
5°	120251
10°	109884
15°	96255
20°	82561
25°	68931
30°	55173
35°	41385
40°	30028
45°	19630
50°	12281
55°	8296
60°	7368
65°	6745
70°	6347
75°	5761
80°	5430
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19630 cd/sqm

TEST NUMBER: P1264918

CATALOG NUMBER: P3AS10R129730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	10.3
10°-20°	118.1	24.1
20°-30°	130.1	26.6
30°-40°	97.5	19.9
40°-50°	50.5	10.3
50°-60°	20.9	4.3
60°-70°	13.0	2.6
70°-80°	7.3	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.7	61.0
0°-40°	396.2	80.9
0°-60°	467.6	95.4
0°-90°	490.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	490.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	564	
5°	546	50
15°	424	118
25°	285	130
35°	155	97
45°	63	51
55°	22	21
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1264918

CATALOG NUMBER: P3AS10R129730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	563.6
1°	564.3
2°	562.4
3°	558.7
4°	553.1
5°	546.3
6°	537.6
7°	528.3
8°	517.1
9°	505.3
10°	493.5
12.5°	459.4
15°	424.0
17.5°	388.6
20°	353.8
22.5°	318.4
25°	284.9
27.5°	251.4
30°	217.9
32.5°	185.0
35°	154.6
37.5°	128.5
40°	104.9
42.5°	83.2
45°	63.3
47.5°	47.8
50°	36.0
52.5°	26.7
55°	21.7
57.5°	19.2
60°	16.8
62.5°	14.9
65°	13.0
67.5°	11.2
70°	9.9
72.5°	8.1
75°	6.8
77.5°	5.6
80°	4.3
82.5°	3.1
85°	1.9
87.5°	0.6
90°	0.0

(END OF REPORT)