

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264947

Luminaire Tested: P3AS13R129730DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129730DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 816.0 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264947

CATALOG NUMBER: P3AS13R129730DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264947

CATALOG NUMBER: P3AS13R129730DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	90	89
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	86	85
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	82	81
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	79	78
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	76	75
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	73	72
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	71	70
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	68	67
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	697071
5°	618753
10°	429696
15°	254122
20°	144726
25°	82723
30°	45779
35°	24414
40°	13511
45°	7319
50°	4571
55°	3594
60°	3114
65°	2854
70°	2500
75°	2626
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7319 cd/sqm

TEST NUMBER: P1264947

CATALOG NUMBER: P3AS13R129730DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.0	29.3
10°-20°	315.5	38.7
20°-30°	162.4	19.9
30°-40°	61.0	7.5
40°-50°	20.0	2.4
50°-60°	8.6	1.1
60°-70°	5.4	0.7
70°-80°	3.2	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.9	87.9
0°-40°	777.9	95.3
0°-60°	806.5	98.8
0°-90°	816.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3179	
5°	2811	239
15°	1119	315
25°	342	162
35°	91	61
45°	24	20
55°	9	9
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1264947

CATALOG NUMBER: P3AS13R129730DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3178.9
1°	3172.6
2°	3131.0
3°	3051.6
4°	2947.0
5°	2811.0
6°	2657.0
7°	2488.0
8°	2300.1
9°	2114.6
10°	1929.8
12.5°	1484.9
15°	1119.4
17.5°	838.0
20°	620.2
22.5°	463.0
25°	341.9
27.5°	249.2
30°	180.8
32.5°	128.1
35°	91.2
37.5°	65.2
40°	47.2
42.5°	33.8
45°	23.6
47.5°	17.3
50°	13.4
52.5°	11.0
55°	9.4
57.5°	7.9
60°	7.1
62.5°	6.3
65°	5.5
67.5°	4.7
70°	3.9
72.5°	3.9
75°	3.1
77.5°	2.4
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)