

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264299

Luminaire Tested: P3AS05R359730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 231.0 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264299

CATALOG NUMBER: P3AS05R359730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264299

CATALOG NUMBER: P3AS05R359730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	69	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116504
5°	111974
10°	97549
15°	74734
20°	49984
25°	30244
30°	17370
35°	9717
40°	5153
45°	2667
50°	1262
55°	994
60°	965
65°	778
70°	833
75°	763
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2667 cd/sqm

TEST NUMBER: P1264299

CATALOG NUMBER: P3AS05R359730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.3	20.0
10°-20°	89.7	38.8
20°-30°	58.7	25.4
30°-40°	23.8	10.3
40°-50°	7.1	3.1
50°-60°	2.4	1.0
60°-70°	1.6	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.7	84.3
0°-40°	218.5	94.6
0°-60°	228.1	98.7
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	531	
5°	509	46
15°	329	90
25°	125	59
35°	36	24
45°	9	7
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264299

CATALOG NUMBER: P3AS05R359730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	531.3
1°	530.4
2°	528.0
3°	523.2
4°	517.5
5°	508.7
6°	497.7
7°	485.4
8°	471.5
9°	455.7
10°	438.1
11°	418.6
12°	398.2
13°	375.3
14°	353.5
15°	329.2
17.5°	270.1
20°	214.2
22.5°	164.8
25°	125.0
27.5°	93.2
30°	68.6
32.5°	50.3
35°	36.3
37.5°	25.7
40°	18.0
42.5°	12.5
45°	8.6
47.5°	5.7
50°	3.7
52.5°	2.9
55°	2.6
57.5°	2.4
60°	2.2
62.5°	2.0
65°	1.5
67.5°	1.3
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.7
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1264299

CATALOG NUMBER: P3AS05R359730DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)