

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264985

Luminaire Tested: P3AS13R159730DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159730DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 537.0 lumens
Efficiency: N/A
Efficacy: 36.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264985

CATALOG NUMBER: P3AS13R159730DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1264985

CATALOG NUMBER: P3AS13R159730DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231560
5°	214021
10°	170872
15°	129081
20°	98289
25°	74908
30°	53654
35°	35014
40°	21469
45°	12994
50°	8631
55°	6652
60°	5745
65°	4981
70°	4488
75°	4406
80°	3283
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12994 cd/sqm

TEST NUMBER: P1264985

CATALOG NUMBER: P3AS13R159730DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	16.0
10°-20°	158.9	29.6
20°-30°	141.5	26.3
30°-40°	83.7	15.6
40°-50°	34.4	6.4
50°-60°	16.1	3.0
60°-70°	9.8	1.8
70°-80°	5.2	1.0
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.5	72.0
0°-40°	470.3	87.6
0°-60°	520.7	97.0
0°-90°	537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	972	86
15°	569	159
25°	310	141
35°	131	84
45°	42	34
55°	17	16
65°	10	10
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1264985

CATALOG NUMBER: P3AS13R159730DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1056.0
1°	1053.4
2°	1045.6
3°	1029.9
4°	1003.7
5°	972.3
6°	938.3
7°	898.2
8°	856.3
9°	813.6
10°	767.4
12.5°	661.9
15°	568.6
17.5°	488.3
20°	421.2
22.5°	361.9
25°	309.6
27.5°	259.0
30°	211.9
32.5°	169.2
35°	130.8
37.5°	100.3
40°	75.0
42.5°	55.8
45°	41.9
47.5°	32.3
50°	25.3
52.5°	20.9
55°	17.4
57.5°	14.8
60°	13.1
62.5°	11.3
65°	9.6
67.5°	8.7
70°	7.0
72.5°	6.1
75°	5.2
77.5°	3.5
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)