

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265007

Luminaire Tested: P3AS13R209730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 336.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265007

CATALOG NUMBER: P3AS13R209730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265007

CATALOG NUMBER: P3AS13R209730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83107
5°	80893
10°	74414
15°	65494
20°	56168
25°	47204
30°	38158
35°	29018
40°	20639
45°	13645
50°	8460
55°	5543
60°	5043
65°	4670
70°	4360
75°	3982
80°	3788
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13645 cd/sqm

TEST NUMBER: P1265007

CATALOG NUMBER: P3AS13R209730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.0	10.1
10°-20°	80.3	23.9
20°-30°	89.2	26.5
30°-40°	68.0	20.2
40°-50°	34.8	10.4
50°-60°	14.3	4.3
60°-70°	8.9	2.7
70°-80°	5.0	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.5	60.6
0°-40°	271.5	80.8
0°-60°	320.6	95.4
0°-90°	336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	336.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	379	
5°	368	34
15°	288	80
25°	195	89
35°	108	68
45°	44	35
55°	14	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1265007

CATALOG NUMBER: P3AS13R209730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	379.0
1°	379.4
2°	377.7
3°	375.6
4°	372.2
5°	367.5
6°	361.9
7°	356.0
8°	349.6
9°	341.9
10°	334.2
12.5°	312.0
15°	288.5
17.5°	264.6
20°	240.7
22.5°	216.8
25°	195.1
27.5°	173.3
30°	150.7
32.5°	129.3
35°	108.4
37.5°	90.1
40°	72.1
42.5°	56.8
45°	44.0
47.5°	33.3
50°	24.8
52.5°	18.4
55°	14.5
57.5°	13.2
60°	11.5
62.5°	10.2
65°	9.0
67.5°	7.7
70°	6.8
72.5°	5.5
75°	4.7
77.5°	3.8
80°	3.0
82.5°	2.1
85°	1.3
87.5°	0.4
90°	0.0

(END OF REPORT)