

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265014

Luminaire Tested: P3AS13R209730DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209730DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 787.0 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265014

CATALOG NUMBER: P3AS13R209730DE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1265014

CATALOG NUMBER: P3AS13R209730DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	104	103	101	100	100	98	98	98
2	113	110	107	105	111	108	106	104	105	104	102	102	101	100	100	99	98	97	97	97
3	110	107	104	101	109	105	103	101	103	101	99	101	99	98	99	97	96	95	95	95
4	108	104	101	98	107	103	100	98	101	98	97	99	97	95	97	96	94	93	93	93
5	106	101	98	96	105	100	97	95	99	96	94	97	95	94	96	94	93	92	92	92
6	104	99	96	93	103	98	95	93	97	94	93	96	94	92	95	93	91	91	91	91
7	102	97	94	92	101	96	93	91	95	93	91	94	92	90	94	92	90	89	89	89
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88	88	88
9	99	94	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87	87	87
10	97	92	89	87	96	92	89	87	91	88	87	91	88	87	90	88	86	86	86	86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1564962
5°	1202000
10°	740512
15°	215506
20°	28749
25°	8517
30°	2557
35°	348
40°	372
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1265014

CATALOG NUMBER: P3AS13R209730DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	454.8	57.8
10°-20°	310.2	39.4
20°-30°	19.9	2.5
30°-40°	2.0	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	784.9	99.7
0°-40°	786.9	100.0
0°-60°	787.0	100.0
0°-90°	787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7137	
5°	5461	455
15°	949	310
25°	35	20
35°	1	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265014

CATALOG NUMBER: P3AS13R209730DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7136.8
2.5°	6435.2
5°	5460.7
7.5°	4380.7
10°	3325.7
12.5°	2086.0
15°	949.3
17.5°	300.5
20°	123.2
22.5°	65.4
25°	35.2
27.5°	17.6
30°	10.1
32.5°	5.0
35°	1.3
37.5°	1.3
40°	1.3
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)