

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265039

Luminaire Tested: P3AS13R259730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265039

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265039

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166368
5°	162403
10°	150476
15°	134030
20°	115183
25°	97893
30°	80595
35°	62801
40°	45170
45°	28654
50°	16955
55°	11660
60°	10701
65°	9962
70°	8976
75°	8133
80°	7703
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28654 cd/sqm

TEST NUMBER: P1265039

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	9.8
10°-20°	163.9	23.4
20°-30°	185.2	26.5
30°-40°	146.5	20.9
40°-50°	74.0	10.6
50°-60°	29.6	4.2
60°-70°	19.0	2.7
70°-80°	10.5	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	417.5	59.6
0°-40°	564.0	80.6
0°-60°	667.6	95.4
0°-90°	700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	759	
5°	738	68
15°	590	164
25°	405	185
35°	235	146
45°	92	74
55°	30	30
65°	19	19
75°	10	10
85°	3	3
90°	0	

TEST NUMBER: P1265039

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	758.7
1°	758.7
2°	756.1
3°	751.7
4°	745.6
5°	737.8
6°	728.2
7°	716.8
8°	704.6
9°	690.7
10°	675.8
11°	659.3
12°	643.6
13°	625.3
14°	607.8
15°	590.4
17.5°	541.5
20°	493.6
22.5°	448.2
25°	404.6
27.5°	361.9
30°	318.3
32.5°	277.3
35°	234.6
37.5°	195.3
40°	157.8
42.5°	123.0
45°	92.4
47.5°	68.9
50°	49.7
52.5°	37.5
55°	30.5
57.5°	27.9
60°	24.4
62.5°	21.8
65°	19.2
67.5°	16.6
70°	14.0
72.5°	12.2
75°	9.6
77.5°	7.8
80°	6.1
82.5°	4.4
85°	2.6
87.5°	0.9



TEST NUMBER: P1265039

CATALOG NUMBER: P3AS13R259730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)