

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265067

Luminaire Tested: P3AS13R309730DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265067  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R309730DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 710.0 lumens  
Efficiency: N/A  
Efficacy: 48.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265067  
CATALOG NUMBER: P3AS13R309730DE010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1265067  
 CATALOG NUMBER: P3AS13R309730DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	167728
5°	163966
10°	152480
15°	135687
20°	116700
25°	98861
30°	82063
35°	64380
40°	46144
45°	30267
50°	17228
55°	11316
60°	10701
65°	9962
70°	8912
75°	8133
80°	7703
85°	6542

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30267 cd/sqm



TEST NUMBER: P1265067  
 CATALOG NUMBER: P3AS13R309730DE010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.2	9.7
10°-20°	166.2	23.4
20°-30°	187.2	26.4
30°-40°	149.5	21.1
40°-50°	76.8	10.8
50°-60°	28.9	4.1
60°-70°	19.0	2.7
70°-80°	10.2	1.4
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.5	59.5
0°-40°	572.1	80.6
0°-60°	677.8	95.5
0°-90°	710.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	765	
5°	745	69
15°	598	166
25°	409	187
35°	240	150
45°	98	77
55°	30	29
65°	19	19
75°	10	10
85°	3	3
90°	0	

TEST NUMBER: P1265067

CATALOG NUMBER: P3AS13R309730DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	764.9
1°	764.9
2°	762.3
3°	758.0
4°	751.9
5°	744.9
6°	736.2
7°	724.9
8°	712.7
9°	698.7
10°	684.8
11°	669.1
12°	652.6
13°	635.1
14°	616.8
15°	597.7
17.5°	548.9
20°	500.1
22.5°	453.0
25°	408.6
27.5°	365.0
30°	324.1
32.5°	282.3
35°	240.5
37.5°	199.5
40°	161.2
42.5°	127.2
45°	97.6
47.5°	72.3
50°	50.5
52.5°	35.7
55°	29.6
57.5°	27.0
60°	24.4
62.5°	21.8
65°	19.2
67.5°	16.6
70°	13.9
72.5°	11.3
75°	9.6
77.5°	7.8
80°	6.1
82.5°	4.4
85°	2.6
87.5°	0.9



TEST NUMBER: P1265067  
CATALOG NUMBER: P3AS13R309730DE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)