

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264362

Luminaire Tested: P3AS05R459730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 191.0 lumens
Efficiency: N/A
Efficacy: 26.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264362

CATALOG NUMBER: P3AS05R459730DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1264362

CATALOG NUMBER: P3AS05R459730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40501
5°	39775
10°	37630
15°	34325
20°	30359
25°	26372
30°	22636
35°	18846
40°	14055
45°	8590
50°	3991
55°	3097
60°	2982
65°	2750
70°	2565
75°	2457
80°	2273
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8590 cd/sqm

TEST NUMBER: P1264362

CATALOG NUMBER: P3AS05R459730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.9	8.8
10°-20°	42.1	22.0
20°-30°	50.0	26.2
30°-40°	43.5	22.7
40°-50°	21.8	11.4
50°-60°	7.6	4.0
60°-70°	5.3	2.8
70°-80°	3.0	1.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.0	57.1
0°-40°	152.5	79.8
0°-60°	181.8	95.2
0°-90°	191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	191.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	185	
5°	181	17
15°	151	42
25°	109	50
35°	70	43
45°	28	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1264362

CATALOG NUMBER: P3AS05R459730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	184.7
2.5°	183.8
5°	180.7
7.5°	175.9
10°	169.0
12.5°	160.7
15°	151.2
17.5°	140.7
20°	130.1
22.5°	119.3
25°	109.0
27.5°	99.1
30°	89.4
32.5°	80.1
35°	70.4
37.5°	60.1
40°	49.1
42.5°	38.3
45°	27.7
47.5°	18.3
50°	11.7
52.5°	9.0
55°	8.1
57.5°	7.5
60°	6.8
62.5°	6.2
65°	5.3
67.5°	4.6
70°	4.0
72.5°	3.3
75°	2.9
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)