

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265092

Luminaire Tested: P3AS13R359730DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359730DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 565.0 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265092
CATALOG NUMBER: P3AS13R359730DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1265092
 CATALOG NUMBER: P3AS13R359730DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | | | |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 97 | 93 | 97 | 94 | 91 | 94 | 92 | 89 | 91 | 89 | 87 | 86 | | | |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 84 | 89 | 85 | 82 | 86 | 84 | 81 | 80 | | | |
| 4 | 97 | 89 | 83 | 79 | 95 | 88 | 82 | 78 | 86 | 81 | 77 | 84 | 80 | 77 | 82 | 78 | 76 | 74 | | | |
| 5 | 92 | 83 | 77 | 73 | 90 | 82 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | | | |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 68 | 76 | 71 | 67 | 75 | 70 | 67 | 73 | 69 | 66 | 65 | | | |
| 7 | 83 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 67 | 63 | 71 | 66 | 63 | 69 | 65 | 62 | 61 | | | |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 57 | | | |
| 9 | 76 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 54 | | | |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 61 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 53 | 51 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 181608 |
| 5° | 177129 |
| 10° | 161943 |
| 15° | 137458 |
| 20° | 108813 |
| 25° | 82287 |
| 30° | 59908 |
| 35° | 40529 |
| 40° | 24904 |
| 45° | 14296 |
| 50° | 8597 |
| 55° | 6996 |
| 60° | 6096 |
| 65° | 5396 |
| 70° | 4488 |
| 75° | 4406 |
| 80° | 4420 |
| 85° | 4277 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14296 cd/sqm



TEST NUMBER: P1265092
 CATALOG NUMBER: P3AS13R359730DE010 E3DL1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 74.4 | 13.2 |
| 10°-20° | 166.9 | 29.5 |
| 20°-30° | 156.1 | 27.6 |
| 30°-40° | 95.6 | 16.9 |
| 40°-50° | 37.7 | 6.7 |
| 50°-60° | 16.6 | 2.9 |
| 60°-70° | 10.3 | 1.8 |
| 70°-80° | 5.5 | 1.0 |
| 80°-90° | 1.9 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 397.4 | 70.3 |
| 0°-40° | 493.0 | 87.3 |
| 0°-60° | 547.3 | 96.9 |
| 0°-90° | 565.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 565.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 828 | |
| 5° | 805 | 74 |
| 15° | 606 | 167 |
| 25° | 340 | 156 |
| 35° | 151 | 96 |
| 45° | 46 | 38 |
| 55° | 18 | 17 |
| 65° | 10 | 10 |
| 75° | 5 | 6 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P1265092
CATALOG NUMBER: P3AS13R359730DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 828.2 |
| 1° | 829.1 |
| 2° | 826.5 |
| 3° | 821.2 |
| 4° | 813.4 |
| 5° | 804.7 |
| 6° | 793.4 |
| 7° | 780.3 |
| 8° | 764.7 |
| 9° | 747.3 |
| 10° | 727.3 |
| 11° | 706.4 |
| 12° | 683.8 |
| 13° | 659.4 |
| 14° | 632.5 |
| 15° | 605.5 |
| 17.5° | 535.9 |
| 20° | 466.3 |
| 22.5° | 399.3 |
| 25° | 340.1 |
| 27.5° | 285.3 |
| 30° | 236.6 |
| 32.5° | 191.4 |
| 35° | 151.4 |
| 37.5° | 115.7 |
| 40° | 87.0 |
| 42.5° | 62.6 |
| 45° | 46.1 |
| 47.5° | 33.1 |
| 50° | 25.2 |
| 52.5° | 20.9 |
| 55° | 18.3 |
| 57.5° | 15.7 |
| 60° | 13.9 |
| 62.5° | 12.2 |
| 65° | 10.4 |
| 67.5° | 8.7 |
| 70° | 7.0 |
| 72.5° | 6.1 |
| 75° | 5.2 |
| 77.5° | 4.3 |
| 80° | 3.5 |
| 82.5° | 2.6 |
| 85° | 1.7 |
| 87.5° | 0.9 |



TEST NUMBER: P1265092
CATALOG NUMBER: P3AS13R359730DE010 E3DL1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)