

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264386

Luminaire Tested: P3AS05R509730DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509730DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 504.9 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264386
CATALOG NUMBER: P3AS05R509730DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1264386
 CATALOG NUMBER: P3AS05R509730DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76			
5	93	85	80	76	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	68			
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60			
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57			
10	74	65	59	56	73	65	59	56	64	59	55	63	59	55	62	58	55	54			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160777
5°	157539
10°	147559
15°	132101
20°	111170
25°	84852
30°	55148
35°	32685
40°	18893
45°	9458
50°	3514
55°	2753
60°	2544
65°	2335
70°	2308
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9458 cd/sqm



TEST NUMBER: P1264386
 CATALOG NUMBER: P3AS05R509730DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.6	13.2
10°-20°	160.9	31.9
20°-30°	157.9	31.3
30°-40°	79.5	15.8
40°-50°	25.1	5.0
50°-60°	6.5	1.3
60°-70°	4.6	0.9
70°-80°	2.8	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.4	76.3
0°-40°	464.9	92.1
0°-60°	496.6	98.3
0°-90°	504.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	504.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	733	
5°	716	67
15°	582	161
25°	351	158
35°	122	80
45°	30	25
55°	7	7
65°	4	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1264386
CATALOG NUMBER: P3AS05R509730DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	733.2
2.5°	728.7
5°	715.7
7.5°	692.4
10°	662.7
12.5°	624.6
15°	581.9
17.5°	532.5
20°	476.4
22.5°	415.8
25°	350.7
27.5°	281.5
30°	217.8
32.5°	163.9
35°	122.1
37.5°	90.3
40°	66.0
42.5°	46.7
45°	30.5
47.5°	17.5
50°	10.3
52.5°	7.6
55°	7.2
57.5°	6.3
60°	5.8
62.5°	5.4
65°	4.5
67.5°	4.0
70°	3.6
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)