

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265105

Luminaire Tested: P3AS13R359730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 565.0 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265105

CATALOG NUMBER: P3AS13R359730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265105

CATALOG NUMBER: P3AS13R359730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181608
5°	177129
10°	161943
15°	137458
20°	108813
25°	82287
30°	59908
35°	40529
40°	24904
45°	14296
50°	8597
55°	6996
60°	6096
65°	5396
70°	4488
75°	4406
80°	4420
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14296 cd/sqm

TEST NUMBER: P1265105

CATALOG NUMBER: P3AS13R359730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.4	13.2
10°-20°	166.9	29.5
20°-30°	156.1	27.6
30°-40°	95.6	16.9
40°-50°	37.7	6.7
50°-60°	16.6	2.9
60°-70°	10.3	1.8
70°-80°	5.5	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.4	70.3
0°-40°	493.0	87.3
0°-60°	547.3	96.9
0°-90°	565.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	565.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	828	
5°	805	74
15°	606	167
25°	340	156
35°	151	96
45°	46	38
55°	18	17
65°	10	10
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1265105

CATALOG NUMBER: P3AS13R359730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	828.2
1°	829.1
2°	826.5
3°	821.2
4°	813.4
5°	804.7
6°	793.4
7°	780.3
8°	764.7
9°	747.3
10°	727.3
11°	706.4
12°	683.8
13°	659.4
14°	632.5
15°	605.5
17.5°	535.9
20°	466.3
22.5°	399.3
25°	340.1
27.5°	285.3
30°	236.6
32.5°	191.4
35°	151.4
37.5°	115.7
40°	87.0
42.5°	62.6
45°	46.1
47.5°	33.1
50°	25.2
52.5°	20.9
55°	18.3
57.5°	15.7
60°	13.9
62.5°	12.2
65°	10.4
67.5°	8.7
70°	7.0
72.5°	6.1
75°	5.2
77.5°	4.3
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9



TEST NUMBER: P1265105

CATALOG NUMBER: P3AS13R359730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)